#### WORKS WITH ALL VR APPS

- 1. Download VR App. 2. Follow instructions for VR App.
- 3. Insert phone into VR headset, making sure phone is lined up properly according to center line between split screen images.
- 4. Put on your VR headset, adjusting headstraps to secure in place and wear comfortably.
- 🔽 YouTube VR Videos & all VR apps 📉 Google™ Cardboard 🗽





Download on the App Store

# CONTROLS FOR **IMAGE CLARITY** OBJECT DISTANCE Move FORWARD / BACK FOCAL DISTANCE Slide LEFT / RIGHT



Easy Phone Placement Follow light center line to center phone inside

> \* Phone cannot be in a case (fits up to 6" without a case)

3

### Retractable Earbuds

Pull gently. Do not overextend earbuds.



\*\* Auxiliary cable must be connected to phone before using earbuds.

IWNZZ

## JAUNAM 932U

NOISIV MAJIO

#### **PRECAUTIONS**

- Do not drop VR unit as it may damage the device.
- Avoid any strong impact to VR unit as this may damage the device.
- Do not pull apart or dismantle the VR unit in any way.

#### FAQs

#### Q: VR image is blurry

A: Check the smart phone screen line is lined up to the center. If phone screen is properly centered, adjust focal distance and object distance until images become clear.

#### Q: VR Magnetic control switch does not work

**A:** Make sure the direction on the magnetic control switch and the direction on your phone are positioned on the same horizontal line. Check that the app used to support the magnetic control function is activated.

#### **TECHNICAL SPECIFICATIONS**

Product Name: 3-D VIRTUAL GLASSES

Model: V5-1

Material: ABS + PC Eco-friendly material **Resolution:** Based on the video source **Color Bit:** Based on the video source

**HD Lens:** 42mm diameter

**Zoom-in:** 1.5-2x

**Viewing Angle:** 70°-90° degrees Fits Phone Screen Size: 3.5-6 inches

Compatability: Supports Android and iOS smart phones

Virtual Viewing: Simulates 1000 inch screen display

Focal Distance: Adjustable **Object Distance:** Adjustable

**Dimension:** 7.48" x 5.24" x 4.33" inches

Frequency Response: 20Hz - 20kHz

**Resistance:** 32Ω±15% Sensitivity: -58±3dB

**Earbuds:** Fits in ear canal **Input interface:** 3.5mm

Retractable Earbuds Pull-out Cable Length: 7.5 inches

Cushioning materials: